

# ULTRASONIC-7

## DEGREASER

ULTRASONIC-7 concentrated detergent is a high technology for the cleaning of iron, galvanized steel and aluminum in diving equipment and ultrasound.

ULTRASONIC-7 alkaline liquid detergent with inhibitors for aluminum and galvanized surfaces.

ULTRASONIC-7 Particularly suitable for cleaning and descaling of carbon. To achieve this operation, it should be used with Ultrasonic-A.

### DOSAGE AND METHOD OF USING

ULTRASONIC-7 is used diluted in water at 2% with Ultrasonic-A at 0,5%

### TECHNICAL SPECIFICATIONS

COLOUR: YELLOW

APPEARANCE: FLUID

DILUTION: 80-90 ML. DESTILLED WATER

INDICATOR: BROMOPHENOL BLUE

REACTIVE: SULFURIC ACID SOL. NORMAL 0,1 (H<sub>2</sub> SO<sub>4</sub> 0,1N)

FACTOR: 0,152

CALCULATIONS: cc H<sub>2</sub> SO<sub>4</sub> 0,1N x 0,152 = % ULTRASONIC-7