

ULTRASONIC TENSO

NEUTRAL BOOSTER DETERGENT

ULTRASONIC TENSO is specially formulated for use as an active detergent in cleaning tool by immersion in ultrasonic cleaning machines.

It is used as a booster washing product to increase the cavitation power of acid and alkaline products used in ultrasonic cleaning machines.

DOSE AND WAY OF USE

ULTRASONIC TENSO must be used diluted in water ultrasonic tank at a proportion between 0.1 and 0.5% according to the tenacity of the soil to be removed.

TECHNICAL SPECIFICATIONS

COLOUR: BROWN

APPEARANCE: TRANSPARENT LIQUID

SMELL: CHARACTERISTIC

DENSITY: 1,07 +/- 0,05 g/cm³

PH 1%: 7,2 +/- 0,5

CONTAINS

15 % - 30 % Non ionic surfactants

Preservatives: Methyl isothiazolinone, Benzyl isothiazolone

This product meets the existing legislation on biodegradability and the Sanitary Technical Regulation on Detergents.